

# **ANDRITZ**

Vertical Line Shaft Pumps





# **Customized pump engineering**

## Solutions for customer needs

For over 100 years, ANDRITZ has been a byword for competence and innovation in building centrifugal pumps.

Extensive experience and great flexibility in accommodating our customers' needs have made ANDRITZ a preferred partner on a global scale. Beginning with R&D, continuing with design and manufacture, to after-sales-service, ANDRITZ combines the entire value added chain under one roof.

## Fields of application

In water transport for . . .

- irrigation and drainage
- drinking and industrial water supplies

In power supply as . . .

- cooling water pumps for power stations
- Iflue gas desulphurization pumps

In seawater desalination as . . .

seawater intake pumps


### **Materials know-how**

ANDRITZ Pumps transport many different media. The pumps must have various properties, depending on the medium concerned. That is why the choice of material and suitable finishing are the determining factors in functioning and stability of the pump.


Different materials are used depending on the service conditions and customer requirements: cast iron, cast steel, non-alloyed and low-alloy steel grades, stainless CrNi steel grades, Duplex and Superduplex steel grades.

## **Design variants:**


- Model pull-out or non pull-out
- Impeller radial, semi-axial or axial
- Impeller blades fixed, adjustable or variable during operation
- Flow rates up to 20 m³/sec
- Heads up to 80 m
- Different arrangement variants are used according to customer requirements













# Flexible operating range

### Various impeller shapes

ANDRITZ offers a complete program of impeller shapes for all combinations of delivery rates and heads, according to specific speeds. By varying the trailing edge, high-precision adjustments can be made to the desired duty points.

# Hydraulic impeller blade adjustment

The hydraulic blade adjustment mechanism allows the impeller angle to be varied continuously during operation. Thus, the operator can react promptly to changes in flow rate and head. A servo-cylinder that can be fed with pressure oil from both sides is used to rotate the impeller blades via sliding blocks and adjustment crank handles.





Thus, the pump can be set quickly and easily to the required flow rates and heads. In addition, the adjusting mechanism features long service life and low maintenance requirement.

## **Speed control**

Flow rate and head can also be controlled by means of a continuously variable speed control unit for the drive, using a frequency converter. Here, ANDRITZ has put together the ideal concept for pump, drive motor and frequency converter to optimize efficiency.

## Angle-adjustable blades

By using separately mounted, angle-adjustable impeller blades, it is possible to compensate any uncertainties in the system design. As a result, the efficiency can also be optimized or the duty point altered at a later stage. In this case, the angle of the impeller blade can still be adjusted manually to suit new conditions before installation and start-up.






# Competence to convince you

### **Custom-tailored solutions**

ANDRITZ is a byword for customized pump solutions at the highest level. In the interests of our customers we set no limits on size and flow rate in the development and manufacture of customer-specific pumps.




Our highly qualified and experienced engineers rapidly develop new pumps with the latest CFD tools, including model and inspection tests. Special peripheral conditions, such as the inlet and discharge arrangement of the pumps, can be investigated and optimized.



Experienced experts assist our customers with planning, development, installation, start-up and after-sales service. Engineering, design, material selection and manufacturing all run according to defined standards. The processes are transparent and can be adapted to individual needs.

### R&D in fluid mechanics

Pumps with highest efficiencies and excellent cavitation properties are developed in our own laboratory for fluid mechanics, ASTRÖ, to meet the requirements of our customers.





## Close to our customers



#### **ANDRITZ AG**

Stattegger Strasse 18 8045 Graz, Austria Phone: +43 (316) 6902 2133 Fax: +43 (316) 6902 406 guenter.haiden@andritz.com

www.andritz.com/pumps

All data, information, statements, photographs and graphic illustrations made in this leaflet are without any obligation and raise no liabilities to or form part of any sales contracts of ANDRITZ AG or any affiliates for equipment and/or systems referred to herein. © ANDRITZ AG 2010. All rights reserved. No part of this copyrighted work may be reproduced, modified or distributed in any form or by any means, or stored in any database or retrieval system, without the prior written permission of ANDRITZ AG or its affiliates. Any such unauthorized use for any purpose is a violation of the relevant copyright laws. ANDRITZ AG, Stattegger Strasse 18, 8045 Graz, Austria